

WCY68, WEJTAP Connector

By Burndy
Catalog # [WCY68](#)



Wejtap Assembly, 0.940-0.683 (Run), 0.326-0.257 (Tap),
Installed With yellow Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	

- 350 kcmil
- 397 kcmil
- 400 kcmil
- 450 kcmil
- 477 kcmil
- 500 kcmil
- 550 kcmil
- 556 kcmil
- 600 kcmil
- 636 kcmil
- 650 kcmil
- 700 kcmil

Conductor - AL Str Tap Range	3 AWG-1/0 AWG
Conductor - AL Str Tap	

- 3 AWG
- 2 AWG
- 1 AWG
- 1/0 AWG

Conductor Type	
	• ACSR C Str-Run
	• AL C Str-Run
	• ACSR C Str-Tap
	• AL C Str-Tap

Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil- 556.5 (30/7) Eagle kcmil
--------------------------------	---

Conductor - ACSR Str Run	
	• 300.0 (26/7) Ostrich kcmil
	• 336.4 (18/1) Merlin kcmil
	• 336.4 (26/7) Linnet kcmil
	• 336.4 (30/7) Oriole kcmil
	• 397.5 (18/1) Chickadee kcmil
	• 397.5 (24/7) Brant kcmil
	• 397.5 (26/7) Ibis kcmil
	• 397.5 (30/7) Larkspur kcmil

Conductor - ACSR Str Tap Range	
Conductor - ACSR Str Tap	

- 477.0 (18/1) Pelican kcmil
- 477.0 (24/7) Flicker kcmil
- 477.0 (26/7) Hawk kcmil
- 477. (30/7) Hen kcmil
- 500.0 (30/7) Heron kcmil
- 556.5 (24/7) Parakeet kcmil
- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil
- 4 (7/1) Swanate AWG-1 (6/1) Robin AWG
- 4 (7/1) Swanate AWG
- 3 (6/1) Swallow AWG
- 2 (6/1) Sparrow AWG
- 2 (7/1) Sparate AWG
- 1 (6/1) Robin AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810874806
Material	Aluminum
UPC 12 Digit	781810874806
UPC 14 Digit GTIN	00781810874806

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)

