



WCY68PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY68PB](#)

Conn ANSI CL:AA RUS



Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	• 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil

Conductor - AL Str Tap Range	3 AWG-1/0 AWG
Conductor - AL Str Tap	• 3 AWG • 2 AWG • 1 AWG • 1/0 AWG

Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
----------------	---

Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run	• 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil

Conductor - ACSR Str Tap Range	
--------------------------------	--

Conductor - ACSR Str Tap	
--------------------------	--

- 397.5 (26/7) Ibis kcmil
- 397.5 (30/7) Larkspur kcmil
- 477.0 (18/1) Pelican kcmil
- 477.0 (24/7) Flicker kcmil
- 477.0 (26/7) Hawk kcmil
- 477. (30/7) Hen kcmil
- 500.0 (30/7) Heron kcmil
- 556.5 (24/7) Parakeet kcmil
- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil
- 4 (7/1) Swanate AWG-1 (6/1) Robin AWG
- 4 (7/1) Swanate AWG
- 3 (6/1) Swallow AWG
- 2 (6/1) Sparrow AWG
- 2 (7/1) Sparate AWG
- 1 (6/1) Robin AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870624
Material	Aluminum
UPC 12 Digit	781810870624
UPC 14 Digit GTIN	00781810870624

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)