



WCY69, WEJTAP Connector

By Burndy

Catalog # [WCY69](#)

Wejtap Assembly, 0.940-0.683 (Run), 0.262-0.204 (Tap),
Installed With yellow Booster



Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	• 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run	• 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil

- 397.5 (26/7) Ibis kcmil
 - 397.5 (30/7) Larkspur kcmil
 - 477.0 (18/1) Pelican kcmil
 - 477.0 (24/7) Flicker kcmil
 - 477.0 (26/7) Hawk kcmil
 - 477. (30/7) Hen kcmil
 - 500.0 (30/7) Heron kcmil
 - 556.5 (24/7) Parakeet kcmil
 - 556.5 (26/7) Dove kcmil
 - 556.5 (30/7) Eagle kcmil
- 6 (6/1) Turkey AWG-3 (6/1) Swallow AWG
- 6 (6/1) Turkey AWG
 - 5 (6/1) Thrush AWG
 - 4 (6/1) Swan AWG
 - 4 (7/1) Swanate AWG
 - 3 (6/1) Swallow AWG

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810874851
Material	Aluminum
UPC 12 Digit	781810874851
UPC 14 Digit GTIN	00781810874851

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand