



WCY70PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY70PB](#)



WEJTAP Connector, 0.940 - 0.683 (Run), 0.204 - 0.162 (Tap),
With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Standards - RoHS Compliance	NC
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	• 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
Conductor - AL Str Tap Range	8 AWG-4 AWG
Conductor - AL Str Tap	• 8 AWG • 6 AWG • 4 AWG
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run	• 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil

- 397.5 (24/7) Brant kcmil
 - 397.5 (26/7) Ibis kcmil
 - 397.5 (30/7) Larkspur kcmil
 - 477.0 (18/1) Pelican kcmil
 - 477.0 (24/7) Flicker kcmil
 - 477.0 (26/7) Hawk kcmil
 - 477. (30/7) Hen kcmil
 - 500.0 (30/7) Heron kcmil
 - 556.5 (24/7) Parakeet kcmil
 - 556.5 (26/7) Dove kcmil
 - 556.5 (30/7) Eagle kcmil
- | | |
|--------------------------------|---|
| Conductor - ACSR Str Tap Range | 6 (6/1) Turkey AWG-5 (6/1) Thrush AWG |
| Conductor - ACSR Str Tap | <ul style="list-style-type: none">• 6 (6/1) Turkey AWG• 5 (6/1) Thrush AWG |

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870648
Material	Aluminum
UPC 12 Digit	781810870648
UPC 14 Digit GTIN	00781810870648

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)