



WCY76PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY76PB](#)



Wejtap connector installed with Yellow booster, .889-1.133 Run, .700-.900 (Tap)

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | NC |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Conductor

|                              |                                                                                                                                                                                                                                        |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range | 556.5-1000                                                                                                                                                                                                                             |
| Conductor - AL Str Run       | <ul style="list-style-type: none"><li>• 556.5</li><li>• 600</li><li>• 636</li><li>• 650</li><li>• 700</li><li>• 715.5</li><li>• 750</li><li>• 795.5</li><li>• 800</li><li>• 874.5</li><li>• 900</li><li>• 954</li><li>• 1000</li></ul> |
| Conductor - AL Str Tap Range | 350-650                                                                                                                                                                                                                                |
| Conductor - AL Str Tap       | <ul style="list-style-type: none"><li>• 350</li><li>• 397.5</li><li>• 400</li><li>• 450</li><li>• 477</li><li>• 500</li><li>• 550</li><li>• 556.5</li><li>• 600</li><li>• 636</li><li>• 650</li></ul>                                  |
| Conductor Type               | <ul style="list-style-type: none"><li>• ACSR C Str-Run</li><li>• AL C Str-Run</li><li>• ACSR C Str-Tap</li><li>• AL C Str-Tap</li></ul>                                                                                                |

|                                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACSR Str Run Range | 477.0 (30/7) Hen-795 (30/19) Mallard                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 477.0 (30/7) Hen</li><li>• 556.5 (24/7) Parakeet</li><li>• 556.5 (26/7) Dove</li><li>• 556.5 (30/7) Eagle</li><li>• 605 (24/7) Peacock</li><li>• 605 (26/7) Squab</li><li>• 605 (30/19) Teal</li><li>• 636 (24/7) Rook</li><li>• 636 (26/7) Grosbeak</li><li>• 636 (30/19) Egret</li><li>• 666.6 (24/7) Flamingo</li><li>• 715.5 (54/7) Crow</li><li>• 715.5 (26/7) Starling</li><li>• 715.5 (30/19) Redwing</li><li>• 795 (54/7) Condor</li><li>• 795 (26/7) Drake</li><li>• 795 (30/19) Mallard</li></ul> |
| Conductor - ACSR Str Tap Range | 336.4 (18/1) Merlin-556.5 (24/7) Parakeet                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Conductor - ACSR Str Tap       | <ul style="list-style-type: none"><li>• 336.4 (18/1) Merlin</li><li>• 336.4 (26/7) Linnet</li><li>• 336.4 (30/7) Oriole</li><li>• 397.5 (18/1) Chickadee</li><li>• 397.5 (24/7) Brant</li><li>• 397.5 (26/7) Ibis</li><li>• 397.5 (30/7) Larkspur</li><li>• 477.0 (18/1) Pelican</li><li>• 477.0 (24/7) Flicker</li><li>• 477.0 (26/7) Hawk</li><li>• 477.0 (30/7) Hen</li><li>• 556.5 (24/7) Parakeet</li></ul>                                                                                                                                    |

Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

Dimensions

|                                           |        |
|-------------------------------------------|--------|
| Dimension - G inch                        | 1.9 in |
| Dimension - F Width Center to Center inch | 3.5 in |

General

|            |              |
|------------|--------------|
| Color      | Yellow       |
| Trade Name | WEJTAP™      |
| UPC        | 781810870709 |

|                   |                |                       |   |
|-------------------|----------------|-----------------------|---|
| Material          | Aluminum       | Minimum Pack Quantity | 1 |
| UPC 12 Digit      | 781810870709   | <b>Product Assets</b> |   |
| UPC 14 Digit GTIN | 00781810870709 |                       |   |

Logistics

[Catalog \[English\]](#)



A Hubbell brand