



WCY77PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY77PB](#)



Wejtap connector installed with Yellow booster, .889-.1133 Run, .575-.750 (Tap)

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	250-450
Conductor - AL Str Tap	• 250 • 266.8 • 300 • 336.4 • 350 • 397.5 • 400 • 450
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet

- 556.5 (26/7) Dove
- 556.5 (30/7) Eagle
- 605 (24/7) Peacock
- 605 (26/7) Squab
- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 4/0 (6/1) Penguin-397.5 (24/7) Brant
- 4/0 (6/1) Penguin
- 80 (8/1) Grouse
- 101.8 (12/7) Petrel
- 110.8 (12/7) Minorca
- 134.6 (12/7) Leghorn
- 159 (12/7) Guinea
- 176.9 (12/7) Dotterel
- 190.8 (12/7) Dorking
- 203.2 (16/9) Brahma
- 211.3 (12/7) Cochin
- 266.8 (18/1) Waxwing
- 266.8 (26/7) Owl
- 266.8 (26/7) Partridge
- 300.0 (26/7) Ostrich
- 336.4 (18/1) Merlin
- 336.4 (26/7) Linnet
- 336.4 (30/7) Oriole
- 397.5 (18/1) Chickadee
- 397.5 (24/7) Brant

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.9 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow	Logistics	
Trade Name	WEJTAP™	Minimum Pack Quantity	5
UPC	781810870716	Product Assets	
Material	Aluminum	Catalog [English]	
UPC 12 Digit	781810870716		
UPC 14 Digit GTIN	00781810870716		

