



WCY78PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY78PB](#)



WEJTAP Connector, 1.133 - 0.889 (Run), 0.729 - 0.525 (Tap), With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	4/0-400
Conductor - AL Str Tap	• 4/0 • 250 • 266.8 • 300 • 336.4 • 350 • 397.5 • 400
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

- 605 (30/19) Teal
 - 636 (24/7) Rook
 - 636 (26/7) Grosbeak
 - 636 (30/19) Egret
 - 666.6 (24/7) Flamingo
 - 715.5 (54/7) Crow
 - 715.5 (26/7) Starling
 - 715.5 (30/19) Redwing
 - 795 (54/7) Condor
 - 795 (26/7) Drake
 - 795 (30/19) Mallard
- 3/0 (6/1) Pigeon-336.4 (30/7) Oriole
- 3/0 (6/1) Pigeon
 - 4/0 (6/1) Penguin
 - 80 (8/1) Grouse
 - 101.8 (12/7) Petrel
 - 110.8 (12/7) Minorca
 - 134.6 (12/7) Leghorn
 - 159 (12/7) Guinea
 - 176.9 (12/7) Dotterel
 - 190.8 (12/7) Dorking
 - 203.2 (16/9) Brahma
 - 211.3 (12/7) Cochin
 - 266.8 (18/1) Waxwing
 - 266.8 (26/7) Owl
 - 266.8 (26/7) Partridge
 - 300.0 (26/7) Ostrich
 - 336.4 (18/1) Merlin
 - 336.4 (26/7) Linnet
 - 336.4 (30/7) Oriole

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870723
Material	Aluminum
UPC 12 Digit	781810870723

Logistics

[Catalog \[English\]](#)

Minimum Pack Quantity

5

