



WCY83PB, WEJTAP Connector, Booster Included

By Burndy

Catalog # [WCY83PB](#)

Wejtap connector installed with Yellow booster, .889-.1133 Run,
.257-.398 (Tap)



Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	4-2/0
Conductor - AL Str Tap	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet • 556.5 (26/7) Dove

- 556.5 (30/7) Eagle
- 605 (24/7) Peacock
- 605 (26/7) Squab
- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 4 (7/1) Swanate-1/0 (6/1) Raven

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

- 4 (7/1) Swanate
- 3 (6/1) Swallow
- 2 (6/1) Sparrow
- 2 (7/1) Sparate
- 1 (6/1) Robin
- 1/0 (6/1) Raven

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870778
Material	Aluminum
UPC 12 Digit	781810870778
UPC 14 Digit GTIN	00781810870778

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand