



WCY84, WEJTAP Connector

By Burndy
Catalog # [WCY84](#)



Wejtap Assembly, Installed With Yellow Booster, Sum of diameters: 1.369 (Max), 1.221 (Min)

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	556.5 600 636 650 700 715.5 750 795.5 800 874.5 900 954 1000
Conductor - AL Str Tap Range	6-1/0
Conductor - AL Str Tap	6 4 3 2 1 1/0
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap

Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	477.0 (30/7) Hen 556.5 (24/7) Parakeet 556.5 (26/7) Dove 556.5 (30/7) Eagle 605 (24/7) Peacock 605 (26/7) Squab 605 (30/19) Teal 636 (24/7) Rook 636 (26/7) Grosbeak 636 (30/19) Egret 666.6 (24/7) Flamingo 715.5 (54/7) Crow 715.5 (26/7) Starling 715.5 (30/19) Redwing 795 (54/7) Condor 795 (26/7) Drake 795 (30/19) Mallard
Conductor - ACSR Str Tap Range	6 (6/1) Turkey-1 (6/1) Robin
Conductor - ACSR Str Tap	6 (6/1) Turkey 5 (6/1) Thrush 4 (6/1) Swan 4 (7/1) Swanate 3 (6/1) Swallow 2 (6/1) Sparrow 2 (7/1) Sparate 1 (6/1) Robin

Configuration

Connector Type	Tap
----------------	-----

Dimensions


Dimension - G inch	1.79 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810875605

Type	Wejtap Connector	Minimum Pack Quantity	5
Material	Aluminum	Pallet Quantity	350
UPC 12 Digit	781810875605	Carton Quantity	5
UPC 14 Digit GTIN	00781810875605		

Logistics



Product Assets

[Catalog \[English\]](#)