



WCY84PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY84PB](#)



Wejtap connector installed with Yellow booster, .889-.1133 Run, .203-.333 (Tap)

Features

- WEJTAP Connector, packaged with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	556.5 600 636 650 700 715.5 750 795.5 800 874.5 900 954 1000
Conductor - AL Str Tap Range	6-1/0
Conductor - AL Str Tap	6 4 3 2 1 1/0
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap

Conductor - ACSR Str Run Range 477.0 (30/7) Hen-795 (30/19) Mallard

Conductor - ACSR Str Run

- 477.0 (30/7) Hen
- 556.5 (24/7) Parakeet
- 556.5 (26/7) Dove
- 556.5 (30/7) Eagle
- 605 (24/7) Peacock
- 605 (26/7) Squab
- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard

Conductor - ACSR Str Tap Range 6 (6/1) Turkey-1 (6/1) Robin

Conductor - ACSR Str Tap

- 6 (6/1) Turkey
- 5 (6/1) Thrush
- 4 (6/1) Swan
- 4 (7/1) Swanate
- 3 (6/1) Swallow
- 2 (6/1) Sparrow
- 2 (7/1) Sparate
- 1 (6/1) Robin

Configuration

Connector Type Tap

Dimensions

Dimension - G inch	1.79 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810870785
Type	Wejtap Connector with Booster
Material	Aluminum
UPC 12 Digit	781810870785

Logistics

[Catalog \[English\]](#)

Minimum Pack Quantity

5

