



WCY85, WEJTAP Connector

By Burndy
Catalog # [WCY85](#)



Wejtap Assembly, 1.133-0.889 (Run), 0.258-0.162 (Tap), Installed
With yellow Booster

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	556.5 600 636 650 700 715.5 750 795.5 800 874.5 900 954 1000
Conductor - AL Str Tap Range	8-3
Conductor - AL Str Tap	8 6 4 3
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	477.0 (30/7) Hen

Conductor - ACSR Str Tap Range	556.5 (24/7) Parakeet 556.5 (26/7) Dove 556.5 (30/7) Eagle 605 (24/7) Peacock 605 (26/7) Squab 605 (30/19) Teal 636 (24/7) Rook 636 (26/7) Grosbeak 636 (30/19) Egret 666.6 (24/7) Flamingo 715.5 (54/7) Crow 715.5 (26/7) Starling 715.5 (30/19) Redwing 795 (54/7) Condor 795 (26/7) Drake 795 (30/19) Mallard 6 (6/1) Turkey-3 (6/1) Swallow
Conductor - ACSR Str Tap	6 (6/1) Turkey 5 (6/1) Thrush 4 (6/1) Swan 4 (7/1) Swanate 3 (6/1) Swallow

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810875650
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810875650
UPC 14 Digit GTIN	00781810875650

Logistics

Minimum Pack Quantity	5
Pallet Quantity	350
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)



A Hubbell brand