



WCY90PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY90PB](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 1.159 - 0.868 (Tap), With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600 kcmil-1000 kcmil
Conductor - AL Str Run	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Tap Range	650 kcmil-1000 kcmil
Conductor - AL Str Tap	• 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet kcmil

- 556.5 (26/7) Dove kcmil
 - 556.5 (30/7) Eagle kcmil
 - 605 (24/7) Peacock kcmil
 - 605 (26/7) Squab kcmil
 - 605 (30/19) Teal kcmil
 - 636 (24/7) Rook kcmil
 - 636 (26/7) Grosbeak kcmil
 - 636 (30/19) Egret kcmil
 - 666.6 (24/7) Flamingo kcmil
 - 715.5 (54/7) Crow kcmil
 - 715.5 (24/7) Stilt kcmil
 - 715.5 (26/7) Starling kcmil
 - 715.5 (30/19) Redwing kcmil
 - 795 (54/7) Condor kcmil
 - 795 (26/7) Drake kcmil
 - 795 (30/19) Mallard kcmil
 - 874.5 (54/7) Crane kcmil
 - 900 (54/7) Canary kcmil
 - 954 (45/7) Rail kcmil
 - 954 (54/7) Cardinal kcmil
 - 1033.5 (45/7) Ortolan kcmil
 - 1033.5 (54/7) Curlew kcmil
- | | |
|--------------------------------|---|
| Conductor - ACSR Str Tap Range | 556.5 (24/7) Parakeet kcmil-1590 (54/19) Falcon kcmil |
| Conductor - ACSR Str Tap | <ul style="list-style-type: none">• 556.5 (24/7) Parakeet kcmil• 556.5 (26/7) Dove kcmil• 556.5 (30/7) Eagle kcmil• 605 (24/7) Peacock kcmil• 605 (26/7) Squab kcmil• 605 (30/19) Teal kcmil• 636 (24/7) Rook kcmil• 636 (26/7) Grosbeak kcmil• 636 (30/19) Egret kcmil• 666.6 (24/7) Flamingo kcmil• 715.5 (54/7) Crow kcmil• 715.5 (24/7) Stilt kcmil• 715.5 (26/7) Starling kcmil• 715.5 (30/19) Redwing kcmil• 795 (54/7) Condor kcmil• 795 (26/7) Drake kcmil• 795 (30/19) Mallard kcmil• 874.5 (54/7) Crane kcmil• 900 (54/7) Canary kcmil• 954 (45/7) Rail kcmil• 954 (54/7) Cardinal kcmil• 1033.5 (45/7) Ortolan kcmil• 1033.5 (54/7) Curlew kcmil |

- 1113 (54/19) Finch kcmil
- 1192.5 (45/7) Bunting kcmil
- 1192.5 (54/19) Grackle kcmil
- 1272 (54/19) Pheasant kcmil
- 1351.5 (54/19) Martin kcmil
- 1431 (54/19) Plover kcmil
- 1510.5 (45/7) Nuthatch kcmil
- 1590 (45/7) Lapwing kcmil
- 1590 (54/19) Falcon kcmil

Configuration

Connector Type Tap

Dimensions

Dimension - G inch 1.97 in

Dimension - F Width Center to 3.5 in
Center inch

General

Color Yellow
Trade Name WEJTAP™
UPC 781810870846
Material Aluminum
UPC 12 Digit 781810870846
UPC 14 Digit GTIN 00781810870846

Logistics

Minimum Pack Quantity 5

Product Assets

[Catalog \[English\]](#)

