



# WCY92PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY92PB](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 0.904 - 0.720 (Tap),  
With Yellow Power Booster Assembly

### Features

- WEJTAP Connector
- Yellow Power Booster Included

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | NC |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

|                                |                                                                                                                                                                                                                        |
|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Run Range   | 600-1000                                                                                                                                                                                                               |
| Conductor - AL Str Run         | <ul style="list-style-type: none"><li>• 600</li><li>• 636</li><li>• 650</li><li>• 700</li><li>• 715.5</li><li>• 750</li><li>• 795.5</li><li>• 800</li><li>• 874.5</li><li>• 900</li><li>• 954</li><li>• 1000</li></ul> |
| Conductor - AL Str Tap Range   | 397.5-600                                                                                                                                                                                                              |
| Conductor - AL Str Tap         | <ul style="list-style-type: none"><li>• 397.5</li><li>• 400</li><li>• 450</li><li>• 477</li><li>• 500</li><li>• 550</li><li>• 556.5</li><li>• 600</li></ul>                                                            |
| Conductor Type                 | <ul style="list-style-type: none"><li>• ACSR C Str-Run</li><li>• AL C Str-Run</li><li>• ACSR C Str-Tap</li><li>• AL C Str-Tap</li></ul>                                                                                |
| Conductor - ACSR Str Run Range | 556.5 (24/7) Parakeet-1033.5 (54/7) Curlew                                                                                                                                                                             |
| Conductor - ACSR Str Run       | <ul style="list-style-type: none"><li>• 556.5 (24/7) Parakeet</li><li>• 556.5 (26/7) Dove</li><li>• 556.5 (30/7) Eagle</li></ul>                                                                                       |

|                                |                                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACSR Str Tap Range | 605 (24/7) Peacock                                                                                                                                                                                                                                                                                                                                 |
| Conductor - ACSR Str Tap       | 605 (26/7) Squab                                                                                                                                                                                                                                                                                                                                   |
|                                | 605 (30/19) Teal                                                                                                                                                                                                                                                                                                                                   |
|                                | 636 (24/7) Rook                                                                                                                                                                                                                                                                                                                                    |
|                                | 636 (26/7) Grosbeak                                                                                                                                                                                                                                                                                                                                |
|                                | 636 (30/19) Egret                                                                                                                                                                                                                                                                                                                                  |
|                                | 666.6 (24/7) Flamingo                                                                                                                                                                                                                                                                                                                              |
|                                | 715.5 (54/7) Crow                                                                                                                                                                                                                                                                                                                                  |
|                                | 715.5 (26/7) Starling                                                                                                                                                                                                                                                                                                                              |
|                                | 715.5 (30/19) Redwing                                                                                                                                                                                                                                                                                                                              |
|                                | 795 (54/7) Condor                                                                                                                                                                                                                                                                                                                                  |
|                                | 795 (26/7) Drake                                                                                                                                                                                                                                                                                                                                   |
|                                | 795 (30/19) Mallard                                                                                                                                                                                                                                                                                                                                |
|                                | 874.5 (54/7) Crane                                                                                                                                                                                                                                                                                                                                 |
|                                | 900 (54/7) Canary                                                                                                                                                                                                                                                                                                                                  |
|                                | 954 (54/7) Cardinal                                                                                                                                                                                                                                                                                                                                |
|                                | 1033.5 (54/7) Curlew                                                                                                                                                                                                                                                                                                                               |
| Conductor - ACSR Str Tap Range | 336.4 (26/7) Linnet-477.0 (30/7) Hen                                                                                                                                                                                                                                                                                                               |
| Conductor - ACSR Str Tap       | <ul style="list-style-type: none"><li>• 336.4 (26/7) Linnet</li><li>• 336.4 (30/7) Oriole</li><li>• 397.5 (18/1) Chickadee</li><li>• 397.5 (24/7) Brant</li><li>• 397.5 (26/7) Ibis</li><li>• 397.5 (30/7) Larkspur</li><li>• 477.0 (18/1) Pelican</li><li>• 477.0 (24/7) Flicker</li><li>• 477.0 (26/7) Hawk</li><li>• 477.0 (30/7) Hen</li></ul> |

### Configuration

|                |     |
|----------------|-----|
| Connector Type | Tap |
|----------------|-----|

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - G inch                        | 1.97 in |
| Dimension - F Width Center to Center inch | 3.5 in  |

### General

|                   |                |
|-------------------|----------------|
| Color             | Yellow         |
| Trade Name        | WEJTAP™        |
| UPC               | 781810870860   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810870860   |
| UPC 14 Digit GTIN | 00781810870860 |

Minimum Pack Quantity 5

[Catalog \[English\]](#)



A Hubbell brand