



WCY93PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY93PB](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 0.900 - 0.700 (Tap),
With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600-1000
Conductor - AL Str Run	• 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	397.5-600
Conductor - AL Str Tap	• 397.5 • 400 • 450 • 477 • 500 • 550 • 556.5 • 600
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet-1033.5 (54/7) Curlew
Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle

- 605 (24/7) Peacock
- 605 (26/7) Squab
- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 874.5 (54/7) Crane
- 900 (54/7) Canary
- 954 (54/7) Cardinal
- 1033.5 (54/7) Curlew
- 336.4 (26/7) Linnet-477.0 (30/7) Hen
- 336.4 (26/7) Linnet
- 336.4 (30/7) Oriole
- 397.5 (18/1) Chickadee
- 397.5 (24/7) Brant
- 397.5 (26/7) Ibis
- 397.5 (30/7) Larkspur
- 477.0 (18/1) Pelican
- 477.0 (24/7) Flicker
- 477.0 (26/7) Hawk
- 477.0 (30/7) Hen

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.97 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870877
Material	Aluminum
UPC 12 Digit	781810870877
UPC 14 Digit GTIN	00781810870877

Minimum Pack Quantity 5

[Catalog \[English\]](#)



A Hubbell brand