



Stainless Steel W Die Kit for Copper Connectors #8 AWG-500 kcmil (12 Sets). Color coded for crimping YA and YS types of connectors

By Burndy
Catalog # [WDIEKITCU](#)

6T W Die Kit (12) for Copper

Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W Style (12 sets)

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	Copper: #8 AWG - 500 Kcmil
-----------------	----------------------------

Dimensions

Length	5.5 in
Weight	2.48 lb.
Height	4.7 in
Width	8 in
Dimensions	5.5 in x 8 in x 4.7 in



Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Tool Type	Die Kit, Copper
Die Type	W Die
UPC	781810667798
Type	Die
Material	Stainless Steel
UPC 12 Digit	781810667798
UPC 14 Digit GTIN	00781810667798

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	462
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)