WEEB-BNDJMP6.7, WEEB® Bonding Jumper, 9", 1/4" Mounting Hardware NOT included

By Burndy
Catalog # WEEB-BNDJMP6.7

WEEB® Bonding Jumper.

Application

WEEB Bond Jumpers are constructed of corrosion resistant, tin-plated braided copper. They offer an excellent solution to maintain electrical continuity over long spans or air gaps between metal structures. The WEEB washer's patented teeth pierce through most non-conductive coatings and imbed into the underlying metal componenet that it is installed on to and is both UL 467 and UL 270 listed. They are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

General

Item Type	3A
UPC	781810537367
UPC 12 Digit	7818105373677

Dimensions

Bolt Size	1/4 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	N
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

3D Models - WEEB-BNDJMP6.7_MODEL-STEP
3D Models - WEEB-BNDJMP6.7_MODEL-PDF
3D Models - WEEB-BNDJMP6.7_MODEL-IGES
Brochures - WEEB Washer Guide and WEEB Washer Theory
Catalogs - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Product Cross Section Image(s) - BUR_WEEBNDJM_Lineart
Sales Drawings - 50002065

©2024 Hubbell Incorporated. All rights reserved.