



WEEB-DSK516-45, WEEB disk washer, Top Clamp Application

By Burndy
Catalog # [WEEB-DSK516-45](#)

WEEB-DSK516-45, 1.77" WEEB disk washer, Top Clamp Application, 0.32" hole size

Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

Application

WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB's patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.

Specifications

Certification - ETL	Y
Certification - UL Recognized	Y
Certified Listed	UL2703 Recognized
Certification - cULus	N



Industry Standard(s)	UL2703 Recognized
UL Listed	Yes
Certification - CSA Approved	N

Dimensions

Package Height	5.500 in
Length	1.77 in
Package Weight	13.930 lb.
Package Length	12.500 in
Package Width	8.500 in
Dimension - Thread Size	-

General

UPC	621945437869
Item Type	3C
Material	304 Stainless Steel
UPC 12 Digit	621945437869
UPC 14 Digit GTIN	00621945437869

Logistics

Pallet Quantity	100
Carton Quantity	2000

Product Assets

[Catalog \[English\]](#)