




WEEB-LUG-10.3, Lay-in lug with WEEB Washer; Tin Plated Copper Lug, M10 or 3/8" hardware NOT included

By Burndy
Catalog # [WEEB-LUG-10.3](#)

Lay-in lug assembly - 100 per box, 1 assy incl (1) Tin pltd CU lug (1) 1/4-28X5/8 (1)WEEB-11.5



Application

WEEB grounding lugs are high quality solutions for your grounding needs. The tin-plated lug assures minimum contact resistance and protection against corrosion. The low profile allows installation in a variety of positions with one solid or stranded copper wire (14 AWG to 6 AWG), or two copper wires (12 AWG to 10 AWG) secured by a 1/4-28 stainless steel screw, horizontal to the tang. The WEEB® Grounding Lug is installed using stainless steel mounting hardware. When tightened, the WEEB® washer's specialized teeth embed into coated metal surfaces or any electrically conductive metal to establish a reliable electrical connection. Available with or without varying hardware assembled or unassembled. UL467 and UL2703 listed.

General

EU RoHS Indicator	Contact Manufacturer
Item Type	4D
UPC	781810671078
UPC 12 Digit	70781810671077

Dimensions

Bolt Size	5/16 in
Dimension - Thread Size	-

Certifications And Compliance

Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	100
Pallet Quantity	14800

Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50043617](#)
[Sell Sheets - WEEB Grounding Lugs with T-Bolt Option \(\(LI-WIL-SF-EN-00715\)\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-WEEB-LUG-10.3-SPEC-EN | REV 5/2024