



**WEEB-LUG-15.8,Lay-in lug with
WEEB Washer; Tin Plated Copper
Lug, M8 or 5/16" hardware NOT
included**

By Burndy
Catalog # [WEEB-LUG-15.8](#)



WEEB® Grounding Lug

Application

WEEB grounding lugs are high quality solutions for your grounding needs. The tin-plated lug assures minimum contact resistance and protection against corrosion. The low profile allows installation in a variety of positions with one solid or stranded copper wire (14 AWG to 6 AWG), or two copper wires (12 AWG to 10 AWG) secured by a 1/4-28 stainless steel screw, horizontal to the tang. The WEEB® Grounding Lug is installed using stainless steel mounting hardware. When tightened, the WEEB® washer's specialized teeth embed into coated metal surfaces or any electrically conductive metal to establish a reliable electrical connection. Available with or without varying hardware assembled or unassembled. UL467 and UL2703 listed.

General

Item Type	4D
UPC	781810537534
UPC 12 Digit	7818105375344

Dimensions

Bolt Size	5/16 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	N
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50022778](#)
[Sell Sheets - WEEB Grounding Lugs with T-Bolt Option \(\(LI-WIL-SF-EN-00715\)](#)



A proud member of the Hubbell Family.