



WEEB-PMC, WEEB Top Clamp Washer, .31" hole size, Rigid

By Burndy
Catalog # [WEEB-PMC](#)

WEEB-PMC, WEEB Top Clamp Washer, 1.58 IN L, 1.10 IN W , 0.31 IN hole size, Rigid



Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

Application

WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB’s patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.

Specifications

Certification - ETL	Y
Certification - UL Recognized	Y
Standards - RoHS Compliance	CM
Status	
Certified Listed	UL2703 Recognized
Certification - cULus	N

Industry Standard(s)	UL2703 Recognized
UL Listed	Yes
Certification - CSA Approved	N

Dimensions

Package Height	0.750 in
Length	1.58 in
Package Weight	0.610 lb.
Package Length	10.000 in
Package Width	7.000 in
Width	1.1 in
Dimension - Thread Size	-

General

UPC	781810537619
Item Type	3A
Material	304 Stainless Steel
UPC 12 Digit	781810537619
UPC 14 Digit GTIN	00781810537619

Logistics

Pallet Quantity	99999
Carton Quantity	6000

Product Assets

[Catalog \[English\]](#)