



WILEYBRAID18, Cu Braid, 18.00 IN L, 1.20 IN W, M8 or 1/4" Hardware NOT included

By Burndy
Catalog # [WILEYBRAID18](#)

WILEYBRAID18 is an 18" long braid/bonding jumper, hardware not included

Features

- Perfect for tracker applications, galvanized steel or anywhere a WEEB washer is not required

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

Specifications

Certification - ETL	Y
Certification - UL Recognized	Y
Certified Listed	UL2703
Certification - cULus	N
Industry Standard(s)	UL2703
UL Listed	Yes
Certification - CSA Approved	N

Dimensions



Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	1.2 in
Dimension - Thread Size	-
Bolt Size	1/4 in

General

Trade Name	WILEY
UPC	621945434448
Item Type	3B
Material	Copper
UPC 12 Digit	621945434448
UPC 14 Digit GTIN	00621945434448

Logistics

Pallet Quantity	8400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)