



WILEYBRAID36-916, Cu Braid, 36.00 IN L, 1.20 IN W, M14 or 9/16" Hardware NOT included

By Burndy
Catalog # [WILEYBRAID36-916](#)

Wiley Braid; 36"; 9/16" Hardware

Features

- Perfect for tracker applications, galvanized steel or anywhere a WEEB washer is not required

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

Specifications

Industry Standard(s)	UL2703
Certified Listed	UL2703
UL Listed	Yes

Dimensions



Width	1.2 in
Package Height	0.000 in
Length	36 in
Bolt Size	9/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945461154
Material	Copper

Logistics

Pallet Quantity	4200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)