



**WILEYBRAID6-38, Cu Braid, 38.00
IN L, 0.87 IN W, M10 or 3/8"
Hardware NOT included**

By Burndy
Catalog # [WILEYBRAID6-38](#)

WILEY Bonding Jumpers are perfect for tracker applications, galvanized steel, or anywhere a WEEB® washer is not required.

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

General

Item Type	3C
UPC	621945448339
UPC 12 Digit	6219454483399

Dimensions

Bolt Size	3/8 in
Dimension - Length Overall inch	6 in
Dimension - Thread Size	-



Oh No!
IMAGE COMING SOON

Certifications And Compliance

Certified Listed	UL2703
Industry Standard(s)	UL2703
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	10500

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50060880](#)



A proud member of the Hubbell Family.