



WILEYBRAID24, Cu Braid , 76.00 IN L,
0.709 IN W, M6 or 1/4" Hardware NOT
included

By Burndy
Catalog # [WILEYBRAID76](#)

Wiley Braid; 76"; 1/4" Hardware

Features

- Perfect for tracker applications, galvanized steel or anywhere a WEEB washer is not required

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

Specifications

Certification - ETL	No
Industry Standard(s)	UL2703
Certified Listed	UL2703

Dimensions



Width	0.706 in
Package Height	0.000 in
Length	24 in
Bolt Size	1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945490482
Material	Copper

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)