



WILEYBRAID9, Cu Braid , 9.00 IN L, 0.709 IN W, M6 or 1/4" Hardware NOT included

By Burndy
Catalog # [WILEYBRAID9](#)

Wiley Braid

Features

- Perfect for tracker applications, galvanized steel or anywhere a WEEB washer is not required


Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

Specifications

Certification - ETL	Y
Certification - UL Recognized	N
Standards - RoHS Compliance	CM
Status	
Certified Listed	UL2703
Certification - cULus	N
Industry Standard(s)	UL2703
UL Listed	Yes
Certification - CSA Approved	N

Dimensions



Package Height	0.000 in
Length	9 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.1 in
Width	0.709 in
Dimension - Thread Size	-
Bolt Size	1/4 in
Dimensions	9 in x 0.709 in x 0.1 in

General

Trade Name	WILEY
UPC	781810652084
Item Type	3C
Material	Copper
UPC 12 Digit	781810652084
UPC 14 Digit GTIN	00781810652084

Logistics

Pallet Quantity	12600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)