



Stainless Steel W Die, Index K840

By Burndy
Catalog # [WK840](#)

6T W Die, Index K840



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index K840

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	• Aluminum: 2/0 AWG- 4/0 AWG • ACSR: 2/0 AWG- 4/0 AWG
-----------------	---

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Weight	0.12 lb.

Force Related

Crimp Force Capacity	6 ton
----------------------	-------

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Sub Brand	W-DIE
Die Index	K840
Die Type	W Die
UPC	781810440162
Type	W-Die for Hydraulic Crimping Tools (set)
Construction Material - Main Material	Stainless Steel
UPC 12 Digit	781810440162
UPC 14 Digit GTIN	00781810440162

Logistics

Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)