



Stainless Steel Nest and Indenter X-Die, OH25 Profile, Use in OUR840 POPPER™ HYTOOL™ Series

By Burndy
Catalog # [XOH25](#)

6T X Die, OH25 Dieless Profile

Features

- Durable Stainless Steel Material
- Nest and Indenter X Style
- OH25 Dieless Profile

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Force Related

Crimp Force Capacity 6 ton



General

Application - For Use On	Use with OUR840 Crimper
Die Type	X Die
UPC	781810011157
Type	Die
UPC 12 Digit	781810011157
UPC 14 Digit GTIN	00781810011157

Logistics

Package Contents	Die only
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)