



Plier-style Crimp/Cut, #22-10 AWG Bare & Nylon; Cuts CU/AL

By Burndy
Catalog # [Y10D](#)

Plier-style Crimper/Cutter, #22-#10 AWG Bare & Nylon Insulated Conn;
Cuts AL & CU

Features

- One tool for both nylon insulated and bare connectors
- Precision machined wire cutter for aluminum and copper
- Heavy duty forged steel, rust resistant finish

Application

Crimping and Cutting

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No

Conductor

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Dimensions

Package Height	0.000 in
Length	9.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Weight	0.82 lb.

Height	0.5 in
Width	2 in
Dimensions	9.75 in x 2 in x 0.5 in

General

Application - For Use On	#22-10 AWG Insulated and Uninsulated Terminals and Splices
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Plier Hand-held Tool
Product Type	Ratchet and Small Hand Tools
Die Type	Permanent Die Grooves
UPC	781810700860
Type	Crimper and Cutter
Construction Material - Main	Steel Alloy

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)