



Ergo Full Cycle Ratchet Crimper, #12-#2 AWG CU Connectors

By Burndy
Catalog # [Y122CMR](#)



Ergo Full Cycle Ratchet Crimper, #12 - #2 AWG CU Stranded, Solid, & Flex Wire

Features

- Overmolded comfort grip handles
- Easy groove identification with color coded dies
- UL Listed/CSA Certified connections when used with recommended BURN DY terminals/splices
- Die index embossment for all 6 wire ranges
- Emergency release mechanism in case of misalignment or mistaken die choice
- Two different kits are also available with a selection of connectors in a sturdy metal carrying case (Y122CMRKIT and Y122CMRCIKIT)

Application

Crimping

Specifications

Standards - RoHS Compliance	UI
Status	
Buy American Compliant	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

Conductor

Crimping Ranges	Copper: #12 AWG - #2 AWG Stranded, Solid and Flex
-----------------	--

Dimensions

Length	10.38 in
Weight	1.3 lb.
Height	3 in
Width	0.75 in
Dimensions	10.38 in x 0.75 in x 3 in

General

Application - For Use On	#12-2 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Product Type	Ratchet and Small Hand Tools
Die Type	Rotating Die Wheel
UPC	781810659694
UPC 12 Digit	781810659694
UPC 14 Digit GTIN	00781810659694

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)