



Rotating Die, Full Cycle Ratchet Hand Crimper for CU Conn, CU Thin-wall C-Taps

By Burndy
Catalog # [Y1MRTC](#)

Rotating Die, Full Cycle Ratchet Hand Crimper for #8 - #1 AWG CU terminals and splices, #14 - #4 AWG CU Thin-wall C-Taps

Features

- Rotating die is color coded to match color coded connectors
- Molded comfort grips reduce fatigue during continuous use
- Ratchet mechanism assures a complete crimp every time

Application

Crimping

Specifications

Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

Conductor

Crimping Ranges	Copper: #8 AWG - #1 AWG
-----------------	-------------------------

Dimensions

Package Height	0.000 in
Length	10 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in



Weight	1.46 lb.
Height	0.75 in
Width	3 in
Dimensions	10 in x 3 in x 0.75 in

General

Application - For Use On	#8-1 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Product Type	Ratchet and Small Hand Tools
Die Type	Rotating Die Wheel
UPC	781810271292

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only
Carton Quantity	20

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)