



Y262CR, Compression Splice Reducer Adapter, Cu

By Burndy  
Catalog # Y262CR

Copper Reducing Adapter for 2/0 AWG reducing down to #2 AWG, Tin Plated, for use with Long Barrel Splices (not included)

Features

- Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Conductor

|                                   |         |
|-----------------------------------|---------|
| Conductor - Copper Str Run Range  | 2/0 AWG |
| Conductor - Copper Str Run        | 2/0 AWG |
| Conductor - Material              | COPPER  |
| Conductor Type                    | CODE    |
| Conductor - Copper Str Size Range | 2 AWG   |
| Conductor - Copper Str Tap Range  | 2 AWG   |
| Conductor - Copper Str Tap        | 2 AWG   |

Configuration

|                |             |
|----------------|-------------|
| Connector Type | LONG BARREL |
|----------------|-------------|

Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Package Height                    | 0.000 in  |
| Dimension - B Length fraction     | 1-3/8 in  |
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - B Length inch         | 1.50 in   |
| Dimension - Outside Diameter inch | 0.43 in   |

General

|                       |                |
|-----------------------|----------------|
| Feature - Barrel Type | Long           |
| Plated                | Y              |
| Die Index             | 13             |
| UPC                   | 781810030905   |
| Material              | Copper         |
| Plating Type          | Tin Plated     |
| Finish Type           | Tin-Plated     |
| UPC 12 Digit          | 781810030905   |
| UPC 14 Digit GTIN     | 00781810030905 |

Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Pallet Quantity       | 48000 |
| Carton Quantity       | 100   |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)