


Y2827R, Compression Splice Reducer Adapter, Cu

By Burndy
Catalog # [Y2827R](#)



Copper Reducing Adapter for 4/0 AWG down to 3/0 AWG, Tin Plated, for use with Long Barrel Splices (not included)

Features

- Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	#3/0 AWG
Conductor - Copper Str Size	• 3/0 AWG • 4/0 AWG
Conductor - Copper Str Run	4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Copper Str Tap	3/0 AWG

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	44 mm
Dimension - Outside Diameter	0.534 in
Dimension - B Length inch	1.75 in
Dimension - Length Overall	1.75 in

General

Die Index	15
Feature - Barrel Type	Long
Plated	Y
Color Code	Purple
Sub Brand	REDUCER/ADAPTER
UPC	781810001035
Type	Y-R, Compression
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810001035
UPC 14 Digit GTIN	00781810001035

Logistics

Minimum Pack Quantity	1
Pallet Quantity	39200
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)