



4.5-Ton Remote C-Head, Pump/Hose,
6,000 psi, Uses D Dies, MIL-T-7928,
UL/CSA

By Burndy
Catalog # [Y29BH](#)

4.5T Remote C-Head Crimper, 6,000 psi

Features

- Hydraulic coupler
- "C" shaped head

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges Copper #8 - 2/0 AWG
Code/Flex, Copper #8 - 4/0
AWG

Dimensions

Length 10.75 in
Width 1.25 in
Weight 5.0 lb.
Height 3 in
Jaw Width 1.15 in



Dimensions 10.75 in x 1.25 in x 3 in

Force Related

Crimp Force Capacity 4.5 ton

General

Trade Name HYPRESS™
Application - For Use On Copper Insulated and
Uninsulated, MIL-T-7928
Type Crimper
UPC 12 Digit 781810039038
UPC 14 Digit GTIN 00781810039038
Tool Type Remote Hydraulic Crimper
UPC 781810039038
Die Type D Die

Logistics

Package Contents Tool, Metal Case
Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)