




Y3028R, Compression Splice Reducer Adapter, Cu

By Burndy
Catalog # [Y3028R](#)



Copper Reducing Adapter for 300 kcmil down to 4/0 AWG, Tin Plated, for use with Long Barrel Splices (not included)

Features

- Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	300 kcmil
Conductor - Copper Str Run	300 kcmil
Conductor - Material	COPPER
Wire Size	#4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Dimension - B Length inch	2.00 in
Dimension - Outside Diameter inch	0.637 in
Dimension - Length Overall inch	2.00 in

General

Feature - Barrel Type	Long
Plated	Y
Color Code	White
Die Index	17
UPC	781810085172
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810085172
UPC 14 Digit GTIN	00781810085172

Logistics

Minimum Pack Quantity	100
Pallet Quantity	29600
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand