




Y342CR, Compression Splice Reducer Adapter, Cu

By Burndy
Catalog # [Y342CR](#)



Copper Reducing Adapter for 500 kcmil down to #2 AWG, Tin Plated, for use with Long Barrel Splices (not included)

Features

- Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run	500 kcmil
Conductor - Material	COPPER
Wire Size	#2 AWG
Conductor Type	CODE
Conductor - Copper Str Size	2 AWG
Range	
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Tap	2 AWG

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	64 mm
Dimension - B Length inch	2.50 in
Dimension - Outside Diameter	0.821 in
Dimension - Length Overall	2.50 in
inch	

General

Feature - Barrel Type	Long
Plated	Y
Color Code	Brown
Die Index	20
UPC	781810001004
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810001004
UPC 14 Digit GTIN	00781810001004

Logistics

Minimum Pack Quantity	25
Pallet Quantity	8700
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand