



12T Cvrdr C-Head Crimper, #8-750 kcmil
CU/AL, up to 3/4" Ground Rod

By Burndy
Catalog # [Y352](#)

12T Cvrdr C-Head Crimper, Self Cont, U Dies for CU/AL; up to 3/4" Ground Rod

Features

- Comfort grip handles
- Trigger controlled ram release
- Short handle throw
- Rubber covered handles
- 180° head rotation
- C-shaped head
- Hole for lifting eye
- Positive push button die locks
- Rubber body covering
- Built-in automatic 10,000 psi "Blow-Off" pressure release valve
- Rapid ram advance handle
- Y35-2 has rubber covered head

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	• Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices) • Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps) • Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only)
-----------------	--

- Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)

Dimensions

Length	23.25 in
Weight	13.5 lb.
Height	2.75 in
Width	4.75 in
Dimensions	23.25 in x 4.75 in x 2.75 in

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	• Copper, N30-N500 Navy, Flex: #8-750 kcmil • Aluminum: #8-750 kcmil • Grounding Taps: Copper #8-500 kcmil • Ground Rod: up to 3/4"
Trade Name	HYPRESS™
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Product Type	12-Ton
Die Type	U Die
UPC	781810408445
Type	Crimper
UPC 12 Digit	781810408445
UPC 14 Digit GTIN	00781810408445

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

Product Assets

[Catalog \[English\]](#)