



12T Remote C-Head Crimper, 10K psi, U Dies, CU/AL, Ground Rod

By Burndy
Catalog # [Y35BH](#)

12T Remote C-Head Crimper, 10,000 psi, U Dies, #8-750 kcmil CU/AL, up to 3/4" Ground Rod

Features

- Lifting eye
- 0.95" jaw opening
- Uses U style dies
- Positive die lock buttons

Application

Crimping

Specifications

Standards - RoHS Compliance Status	EX
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	• Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices) • Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps) • Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only) • Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)
-----------------	---



Dimensions

Length	2.62 in
Weight	8 lb.
Height	9.25 in
Width	4.75 in
Jaw Width	0.95 in
Dimension - Length Overall inch	9.75 in
Dimensions	2.62 in x 4.75 in x 9.25 in

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod
Trade Name	HYPRESS™
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimper
Product Type	12-Ton
Die Type	U Die
UPC	781810408452
UPC 12 Digit	781810408452
UPC 14 Digit GTIN	00781810408452

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

Product Assets

[Catalog \[English\]](#)