



# 12-Ton Remote Covered C-Head Crimper, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod

By Burndy  
Catalog # Y35BH4



12T Remote Covered C-Head Crimper, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod.

### Features

- Lifting eye
- 0.95" jaw opening
- Uses U style dies
- Positive die lock buttons

### Application

Crimping

### General

|                          |                                                                                                                                |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| Application - For Use On | Copper, N30-N500 Navy, Flex: #8-750 kcmil; Aluminum: #8-750 kcmil; Grounding Taps: Copper #8-500 kcmil; Ground Rod: up to 3/4" |
| Catalog Number           | Y35BH4                                                                                                                         |
| Crimp Force Capacity     | 12 ton                                                                                                                         |
| Die Type                 | U Die                                                                                                                          |
| Tool Type                | Remote Hydraulic Crimper                                                                                                       |
| Trade Name               | HYPRESS™                                                                                                                       |
| Type                     | Crimper                                                                                                                        |
| UPC                      | 781810408438                                                                                                                   |
| UPC 14 Digit GTIN        | 00781810408438                                                                                                                 |

### Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 2.62 in x 4.75 in x 9.25 in |
| Height     | 9.25 in                     |
| Jaw Width  | 0.95 in                     |
| Length     | 2.62 in                     |
| Weight     | 8 lb                        |
| Width      | 4.75 in                     |

### Conductor Related

|                 |                                                                                                                                                                                                                                                                                                                                                                                                   |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Crimping Ranges | Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only) |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | EX |
|------------------------------------|----|

### Logistics

|                       |                  |
|-----------------------|------------------|
| Minimum Pack Quantity | 1                |
| Package Contents      | Tool, Metal Case |

### Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_Y35BH\\_LineArt](#)  
[Sales Drawings - SE209028-01](#)  
[Specifications - Y35BH4](#)