



11-Ton Dieless Remote C-Head Crimper with Female Couplers

By Burndy
Catalog # [Y444SBHF](#)

11T Remote Dieless C-Head, Female Cplrs



Features

- C-Head, Dieless System with Range Taking Capability
- #4 -1000 kcmil Cu & Al, #4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation
- Unique 444S Crimp Embossment
- Connections are UL Listed to UL 486A-486B on Copper and Aluminum terminals and splices. Comply with ANSI C119.4 on YDS-RL and YDS-RLNI Splices (ACSR, AAC, AAAC, ACAR). Qualified for use on YCP-L Compression Pulling Heads.

Application

Crimping

Dimensions

Weight	10.50 lb.
Height	16.9 in
Width	13.7 in
Length	3.2 in
Dimensions	3.2 in x 13.7 in x 16.9 in

Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Tool Type	Remote Hydraulic Crimper
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Die Type	Dieless
UPC	621945488038
Trade Name	HYPRESS™
Type	Crimper

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

[Catalog \[English\]](#)