



15T Remote C-Head Crimper, 10000 psi, Uses S Dies

By Burndy
Catalog # [Y45](#)

15-Ton Remote C-Head Crimper, Operating Pressure 10K psi, Uses S Dies

Features

- Large jaw opening
- Quick disconnect hydraulic fitting
- C-Shaped hook style head
- Heavy duty reinforced forged steel body

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Tension Sleeves: Copper #8 sol. - 500 kcmil, Aluminum #6 sol. - 954 kcmil, ACSR #4 - 795 (26/7) kcmil
 - Taps: Aluminum #14 - 954 (18/1) kcmil, ACSR #6 - 795 (54/7) kcmil
 - Aerial Cable Connectors: Copper #6 str. - 1500 kcmil, Aluminum #4 str. - 1000 kcmil
 - HYGROUND® Compression Grounding: Copper #6 - 500 kcmil, 1/2" - 1" ground rods
 - Code Cable Terminals/Splices: Copper #8 - 1500 kcmil, Aluminum #8 - 1000 kcmil



- Code Cable Taps: Copper #14 - 1000 kcmil, Aluminum #14 - 900 kcmil

Dimensions

Length 15.25 in
Weight 15.5 lb.
Height 0.00 in
Width 4.5 in

Force Related

Crimp Force Capacity 15 ton

General

Application - For Use On Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod

Trade Name HYPRESS™

Tool Type Remote Hydraulic Crimper

Product Type 15-Ton

Die Type S Die and U Die with PT6515 Adapter

UPC 781810625156

UPC 12 Digit 781810625156

UPC 14 Digit GTIN 00781810625156

Logistics

Package Contents Tool, Nylon Carry Bag

Product Assets

[Catalog \[English\]](#)