



15-Ton Remote Covered C-Head Crimper, 10000 psi, Uses P and U Dies with PUADP1 Adapter

By Burndy
Catalog # [Y46CLWSBH](#)

15T Remote C-Head, Covered, 10,000 psi

Features

- 2" jaw opening
- Used with P dies and U dies with PUADP1 adapter (sold separately)
- Positive push button die locks
- Light weight scoop style open head design with rubber cover

Application

Crimping

Specifications

Standards - RoHS Compliance UI
Status

Dimensions

Length	14.68 in
Width	2.88 in
Weight	14.5 lb.
Height	5 in
Dimensions	14.68 in x 2.88 in x 5 in



Force Related

Crimp Force Capacity 15 ton

General

Trade Name	HYPRESS™
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Type	Crimper
UPC 12 Digit	781810673744
UPC 14 Digit GTIN	00781810673744
Tool Type	Remote Hydraulic Crimper
UPC	781810673744
Die Type	P Die and U Die with PUADP1 Adapter

Logistics

Package Contents	Tool, Nylon Carry Bag
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)