



15-Ton Remote Latch Head Crimper, 10000 psi, Female Coupler, Uses P and U Dies with PUADP1 Adapter

By Burndy
Catalog # [Y46LWBHF](#)

15T Remote Latch Head, 10K psi, Female

Features

- 2" ram travel
- Used with P dies
- U dies with PUADP1 adapter
- Positive push button die locks
- Light weight latch head design

Application

Crimping

Specifications

Standards - RoHS Compliance UI
Status

Conductor

- Crimping Ranges
- Copper - #8 AWG Str. - 1500 kcmil
 - Aluminum - #8 AWG - 1250 kcmil

Dimensions

Length	14.88 in
Width	3.07 in
Weight	12.4 lb.
Height	5 in



Dimensions14.88 in x 3.07 in x 5 in

Force Related

Crimp Force Capacity15 ton

General

Trade Name	HYPRESS™
Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Type	Crimper
UPC 12 Digit	781810673737
UPC 14 Digit GTIN	00781810673737
Tool Type	Remote Hydraulic Crimper
UPC	781810673737
Die Type	P Die and U Die with PUADP1 Adapter

Logistics

Package Contents	Tool, Nylon Carry Bag
Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	44

Product Assets

[Catalog \[English\]](#)