



15-Ton Remote C-Head Crimper, 10000 psi, Female Coupler.

By Burndy
Catalog # [Y46LWSBHF](#)



15T Remote C-Head Crimper, 10000 psi, Female Coupler.

Features

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter
- Positive push button die locks
- Light weight scoop style open head design

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Catalog Number	Y46LWSBHF
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810673720
UPC 14 Digit GTIN	00781810673720

Dimensions

Dimensions	14.68 in x 2.88 in x 5.00 in
------------	------------------------------

Height	5 in
Length	14.68 in
Weight	14.5 lb
Width	2.88 in

Conductor Related

Crimping Ranges	Copper - #8 AWG Str. - 1500 kcmil; Aluminum - #8 AWG - 1250 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance	UI
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Nylon Carry Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50024880](#)
- [Specifications - Y46LWSBHF](#)



A Hubbell brand