



6-Ton 4-POINT® Series, Dieless C-Head Crimper

By Burndy
Catalog # [Y4PC834](#)

6-Ton 4-POINT® Series, Dieless Hyd C-Head Crimper, Range Taking Capabilities

Features

- 360° head rotation
- Dieless System
- Range taking capabilities
- Handle trigger release

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges Copper Terminals: #8-1000 kcmil
Copper Splices: #8-500 kcmil
Copper Flex Terminals: #8-777.7 Flex
Copper Flex Splices: #8-500 kcmil
Aluminum Terminals: #8-750 kcmil
Aluminum Splices: #8-350 kcmil*
*1.06" barrel diameter maximum for aluminum splices due to jaw opening
Aluminum HYPLUG™: #8-750 kcmil

Dimensions



Length 25.6 in
Weight 11.85 lb.
Height 7.7 in
Width 2.5 in
Dimensions 25.6 in x 2.5 in x 7.7 in

Force Related

Crimp Force Capacity 6 ton

General

Application - For Use On Copper, Aluminum Terminals and Splices, HYPLUG™
Trade Name 4-POINT®
Series 4-POINT® Series
Tool Type Self-Contained Hydraulic Crimper
Product Type 6-Ton 4-POINT® Indenter
Die Type Dieless
UPC 781810456576
Type Crimper
UPC 12 Digit 781810456576
UPC 14 Digit GTIN 00781810456576

Logistics

Package Contents Tool, Plastic Case

Product Assets

[Catalog \[English\]](#)