



60-Ton Remote Latch Head Hydraulic
Crimper, Single Action Ram, 10000 psi,
Uses L Dies.

By Burndy
Catalog # [Y60BHU](#)

60T HYPRESS™ 9600 psi to 10400, Single

Features

- Remote power operated
- Used with BURNDY L, wide L style dies

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Length	11.31 in
Weight	70 lb.
Height	16.62 in
Width	6.75 in
Dimensions	11.31 in x 6.75 in x 16.62 in

Force Related

Crimp Force Capacity 60 ton



General

Application - For Use On	• Copper, Aluminum, ACSR Terminals and Splices • Transmission and Distribution Connectors
Life Expectancy	50,000 cycles min.
Trade Name	HYPRESS™
Tool Type	Remote Hydraulic Crimper
Die Type	L Die
UPC	781810010358
Type	Crimper
UPC 12 Digit	781810010358
UPC 14 Digit GTIN	00781810010358

Logistics

Package Contents Tool, Metal Case

Product Assets

[Catalog \[English\]](#)