



60T Remote Latch Head Crimper, Single Action, 10000 psi

By Burndy
Catalog # [Y60LW](#)

60T Remote Latch Head Crimper, Single Action Ram, 10K psi, Stand & Case



Features

- Remote power operated
- Used with BURNDY L, wide L style dies, and HPS/Fargoequivalent 60 ton dies
- Base stand and metal carry case (for head only) included
- Side lift handle
- Single Acting Ram With Heavy Duty Return Spring
- Fast Easy Die Changing And Secure Die Positioning With Positive Die Release Locking Pins

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

- Crimping Ranges
- Transmission and distribution connectors tension sleeves - Copper: 1/0 STR. - 1000 kcmil, Aluminum: 1/0 STR. - 2300 kcmil, ACSR: 1/0 STR. - 2156 (84/19 STR.)
 - Aerial - Copper: 4/0 STR. - 2500 kcmil, Aluminum: 3/0 STR. - 2500 kcmil

Dimensions

Length	8 in
Weight	43 lb.
Height	18 in
Width	8 in
Dimensions	8 in x 8 in x 18 in

Force Related

Crimp Force Capacity	60 ton
----------------------	--------

General

Application - For Use On	• Copper, Aluminum, ACSR Terminals and Splices • Transmission and Distribution Connectors
Trade Name	HYPRESS™
Tool Type	Remote Hydraulic Crimper
Product Type	60-Ton
Die Type	L Die
UPC	781810545218
UPC 12 Digit	781810545218
UPC 14 Digit GTIN	00781810545218

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Stand, Metal Case
Pallet Quantity	18
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)