



60-Ton Remote Latch Head Hydraulic Crimper, Single Action Ram, 10000 psi, No Stand.

By Burndy
Catalog # [Y60LWLS](#)



60T Remote Latch Head Crimper, Single Action, 10000 psi, No Stand.

Features

- Remote power operated
- Side lift handle
- Single acting ram with heavy duty return spring
- Fast easy die changing and secure die positioning with positive die release locking pins
- Used with BURNDY L, wide L style dies, and HPS/Fargoequivalent 60 ton dies

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices; Transmission and Distribution Connectors
Catalog Number	Y60LWLS
Crimp Force Capacity	60 ton
Die Type	L Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810550083

UPC 14 Digit GTIN 00781810550083

Dimensions

Dimensions	8.00 in x 8.00 in x 12.93 in
Height	12.93 in
Length	8 in
Width	8 in

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Tool, Metal Case
Pallet Quantity	18

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - Y60LWLS](#)



A Hubbell brand