



11T Dieless One-Crimp Latch Head Crimper, Range Taking

By Burndy
Catalog # [Y644HSXT](#)

11-Ton Dieless One-Crimp Latch Head Crimper, Range Taking, Self Cont Hyd



Features

- Ergonomic handle design
- Comfort grip handles
- Handle trigger drain
- 355° head rotation
- Dieless system
- Audible "Pop-Off" pressure relief valve
- Pivoting die nest

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	Copper #6 - 1000 kcmil, Aluminum #6 - 750 kcmil
-----------------	---

Dimensions

Length	23.2 in
Weight	15 lb.
Height	3 in

Width	7.04 in
Dimensions	23.2 in x 7.04 in x 3 in

Force Related

Crimp Force Capacity	11 ton
----------------------	--------

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices, Cable Pulling Heads
Trade Name	HYPRESS™
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Product Type	11-Ton Single Indenter
Die Type	Dieless
UPC	781810458358
Type	Crimper
UPC 12 Digit	781810458358
UPC 14 Digit GTIN	00781810458358

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Plastic Case

Product Assets

[Catalog \[English\]](#)