



12-Ton Remote C-Head Crimper, 10000 psi, U Dies

By Burndy
Catalog # [Y750BHXT](#)

12-Ton Remote Hyd C-Head Crimper, Operating Pressure 10K psi, Uses U Dies

Features

- 355° head rotation
- Used with U style dies
- Exposed positive die lock buttons

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Length 12.8 in
Weight 10.8 lb.
Height 2.9 in
Width 5.2 in
Jaw Width 1.65 in
Dimensions 12.8 in x 5.2 in x 2.9 in

Force Related



Crimp Force Capacity 12 ton

General

Application - For Use On Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding

Trade Name HYPRESS™
Tool Type Remote Hydraulic Crimper
Product Type 12-Ton
Die Type U Die
UPC 781810458594
UPC 12 Digit 781810458594
UPC 14 Digit GTIN 00781810458594

Logistics

Package Contents Tool, Nylon Carry Bag

Product Assets

[Catalog \[English\]](#)