



12T Covered C-Head Crimper, Self Contained, For CU/AL/ACSR

By Burndy
Catalog # [Y750CHSXT](#)

12-Ton Covered C-Head Crimper, Self Cont Hyd, Uses U Dies, CU/AL/ACSR Conn

Features

- Ergonomic handle design
- Comfort grip handles
- Handle trigger drain
- 355° head rotatiaon
- Both die release buttons exposed
- Audible "Pop-Off" pressure relief valve
- Large 1.65" jaw opening

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Dimensions

Length	23.96 in
Weight	17.2 lb.
Height	2.9 in
Width	8.71 in
Jaw Width	1.65 in
Dimensions	23.96 in x 8.71 in x 2.9 in

Force Related

Crimp Force Capacity	12 ton
----------------------	--------

General

Application - For Use On	Tension Sleeves, Taps, Aerial Cable, Terminals & Splices, HYGROUND® Compression Grounding
Trade Name	HYPRESS™
Tool Type	Self-Contained Hydraulic Crimper
Product Type	12-Ton
Die Type	U Die
UPC	781810464335
Type	Crimper
UPC 12 Digit	781810464335
UPC 14 Digit GTIN	00781810464335

Logistics

Package Contents	Tool, Plastic Case
------------------	--------------------

Product Assets

[Catalog \[English\]](#)